

| KVA | CATALOG NUMBER | TAPS FCAN | TAPS FCBN | DESIGN TYPE | TEMP RISE °C | H | W | D | WEIGHT LBS | FRAME NUMBER | WIRING DIAGRAM | WEATHER SHIELD |
|--|----------------|-----------|-----------|-------------|--------------|-------|-------|-------|------------|--------------|----------------|----------------|
| GROUP "J": PRI: 480Δ SEC: 208Y/120 60HZ DOE 2016 | | | | | | | | | | | | |
| 3 | G003K3QH8A03 | - | 4 | 3E | 115 | 13.40 | 15.93 | 8.25 | 116 | 201 | FF | |
| 6 | G006K3QH8A03 | - | 4 | 3E | 115 | 15.90 | 16.93 | 10.00 | 165 | 200 | FF | |
| 6 | G006K3QH3A03 | 8 | 8 | 3E | 115 | 15.90 | 16.93 | 10.00 | 165 | 200 | GG | |
| 9 | G009K3QH8A03 | - | 4 | 3E | 115 | 15.90 | 16.93 | 10.00 | 185 | 103 | FF | |
| 9 | G009K3QH5A03 | - | 5 | 3E | 115 | 15.90 | 16.93 | 10.00 | 185 | 103 | HH | |
| 9 | G009K3QH3A03 | 8 | 8 | 3E | 115 | 15.90 | 16.93 | 10.00 | 185 | 103 | GG | |
| 15 | G015K3QH8A03 | - | 4 | 3E | 115 | 17.38 | 20.00 | 10.50 | 275 | 95 | FF | |
| 15 | G015K3QH5A03 | - | 5 | 3E | 115 | 17.38 | 20.00 | 10.50 | 275 | 95 | HH | |
| 15 | G015K3QH3A03 | 8 | 8 | 3E | 115 | 17.38 | 20.00 | 10.50 | 275 | 95 | GG | |
| 30 | G030K3QH2A03 | 6 | 6 | 3E | 115 | 26.58 | 21.81 | 11.65 | 422 | 243 | II | |
| 45 | G045K3QH2A03 | 6 | 6 | 3E | 115 | 26.58 | 24.81 | 13.53 | 720 | 244 | II | |
| 75 | G075K3QH2A03 | 6 | 6 | 3E | 115 | 32.00 | 30.30 | 15.70 | 1275 | 245 | II | |
| 15 | G015K5QH2A04 | 6 | 6 | 3V | 150 | 28.00 | 21.88 | 17.75 | 228 | 939 | 280B | WS57MI |
| 30 | G030K5QH2A04 | 6 | 6 | 3V | 150 | 36.88 | 24.88 | 21.13 | 405 | 940 | 280B | WS58MI |
| 45 | G045K5QH2A04 | 6 | 6 | 3V | 150 | 36.88 | 24.88 | 21.13 | 436 | 940 | 280B | WS58MI |
| 75 | G075K5QH2A04 | 6 | 6 | 3V | 150 | 43.00 | 30.50 | 24.00 | 609 | 942 | 280B | WS59MI |
| 112.5 | G112K5QH2A04 | 6 | 6 | 3V | 150 | 51.00 | 34.50 | 31.50 | 970 | 943 | 280B | WS60MI |
| 150 | G150K5QH2A04 | 6 | 6 | 3V | 150 | 51.00 | 34.50 | 31.50 | 1220 | 943 | 280B | WS60MI |
| 225 | G225K5QH2A04 | 6 | 6 | 3V | 150 | 60.00 | 38.00 | 33.50 | 1571 | 944 | 657A | WS61MI |
| 300 | G300K5QH2A04 | 6 | 6 | 3V | 150 | 66.18 | 42.18 | 33.50 | 2157 | 945 | 657A | WS62MI |
| 500 | G500K5QH2A04 | 8 | 8 | 3V | 150 | C/F | C/F | C/F | C/F | C/F | 428B | C/F |
| 750 | G750K5QH2A04 | 6 | 6 | 3V | 150 | C/F | C/F | C/F | C/F | C/F | KK | C/F |

(4) 2 @-5%; (5) 4@-2.5%; (6) 2 @+2.5%, 4@-2.5%; (8) 2@+2.5%, 2@-2.5%