


CONNECTION DIAGRAM



PROVIDED WITH SAFE TOUCH TERMINAL COVERS.
NO INTEGRAL FUSING CAPABILITY.

DIMENSIONS							APPROX.WT. LBS (KG)
	A	B	C	D	E	MTG. SLOTS	
INCHES (MM)	3.38 (86)	3.75 (95)	3.50 (89)	2.44 (62)	3.13 (79)	0.203X0.460 (5.1X11.7)	



CAT.NO. B100-2063-GA			CONST. ENCAPSULATED			 LISTED		
			MODEL GLOBALTRAN					
RATING							 CERTIFIED	
OUTPUT AMPS	0.91/0.46	PRIMARY V	380/400/415		TEMP. CLASS	HZ 50/60		 IEC 61558
VA	100	SECONDARY V	110X220		105°C	REVISION G		