






Transformer Specifications	
PRIMARY VOLTAGE(S)	208/230/400/460/575
SECONDARY VOLTAGE(S)	24/115/230
RATED V.A.	250
RATED FREQUENCY	50/60
INSULATION CLASS	130
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	13.1 LBS

TEST REQUIREMENTS		
WINDING	H6-H5-H4-H3-H2-H1	X4-X3-X2-X1
D.C. VOLTS	208.3-229.8-399.9-459.7-575	25.7-123.6-245.6
LOAD VOLTS	208-230-400-460-575	24-115-230
F.L. AMPS	1.387/0.555	10.42/2.174/1.087
HI-POT	4800V	3000V
EXCITING AMPS	0.37AMPS @ 575 VOLTS, 50HZ	
EXCITING WATTS	30.0	



NOTE:

1. ALL MEASUREMENTS IN INCHES (MM)

LABEL 1

TOP

LABEL 2

CAT. NO. B250-2263-GAF

VA 250 VA HZ 50/60

OUTPUT(VA) 250 VA

*ADMISSIBLE INSTANTANEOUS OUTPUT

DATE

PACKAGED ACCESSORIES			
1			
-			
-			

DATE 6/9/09 DRAWN J.G.V. CHECKED APPROVED

RELEASE DATE CUSTOMER PART NO.

MICRON PART NO. B250-2263-GAFA7777A0 B250-2263-GAFA7777B0

SIZE C SCALE NONE

B250-2263-GAF

A	FORMAT REVISED	AN03744	J.V	6/9/09
ECL	REVISIONS		BY	DATE