


CONNECTION DIAGRAM

CONNECTION TABLE

PRIMARY		SECONDARY			
VOLT	TERM.	VOLT	TERM.	VOLT	TERM.
200	H4-H3	23	X3-X2	110	X3-X1
208	H4-H3	24	X3-X2	115	X3-X1
220	H4-H2	23	X3-X2	110	X3-X1
230	H4-H2	24	X3-X2	115	X3-X1
240	H4-H2	25	X3-X2	120	X3-X1
440	H4-H1	23	X3-X2	110	X3-X1
460	H4-H1	24	X3-X2	115	X3-X1
480	H4-H1	25	X3-X2	120	X3-X1



PROVIDED WITH SAFE TOUCH TERMINAL COVERS.
NO INTEGRAL FUSING CAPABILITY.

DIMENSIONS

APPROX. WT.
LBS
(KG)

	A	B	C	D	E	MTG. SLOTS
INCHES (MM)	4.88 (124)	5.25 (133)	4.50 (114)	3.88 (99)	4.38 (111)	0.313X1.063 (8.0X27.0)



CAT.NO. **B300-2107-GAF**

CONST. **ENCAPSULATED**

MODEL **GLOBALTRAN**

UL LISTED

RATING

SF CERTIFIED

OUTPUT AMPS	12.50/2.61	PRIMARY V	220/220/440, 208/230/460, 240/480	TEMP. CLASS	HZ
VA	300	SECONDARY V	23/110, 24/115, 25/120	130°C	50/60
					REVISION G

CE IEC 61558