


CONNECTION DIAGRAM



PROVIDED WITH SAFE TOUCH TERMINAL COVERS.
NO INTEGRAL FUSING CAPABILITY.

DIMENSIONS							APPROX. WT. LBS (KG)
	A	B	C	D	E	MTG. SLOTS	
INCHES (MM)	5.13 (130)	5.25 (133)	4.50 (114)	4.38 (111)	4.38 (111)	0.313X1.063 (8.0X27.0)	



CAT. NO. M500-2049-GAF		CONST. ENCAPSULATED		LISTED CERTIFIED IEC 61558
		MODEL GLOBALTRAN		
RATING				
OUTPUT AMPS	4.35	PRIMARY V	550/575/600	TEMP. CLASS
VA	500	SECONDARY V	110/115/120	130°C
				HZ 50/60 REVISION G