


**DIMENSIONS: IMPERVITRAN
P/N BEGINNING "B"**



**CONNECTION DIAGRAM:
GROUP "J"**

CONTROL TRANSFORMERS:

All are UL Listed, CSA Certified and 50/60 Hz

GROUP "J"		UPC # 784550	OUTPUT		DIMENSIONS INCHES (MM)										MOUNTING SLOTS		APPROX. WEIGHT					
CATALOG NUMBER	VA		AMPS	A		B		C		D		E		IN	MM	LBS	KG					
VOLTAGE:	IN		MM	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM							
PRI: 208/230/460 SEC: 24/115																						
B050MBT713XK	003901	50	2.08/0.44	3	1/2	83	3	76	2	9/16	65	2	3/16	56	2	1/2	64	.203 X .460	5 X 12	3.4	1.6	
B050MBT713RK	003888								3	15/16	99											
B075MBT713XK	005967	75	3.13/0.65	3	5/8	92	3	3/8	86	2	7/8	73	2	7/16	61	2	13/16	71	.203 X .460	5 X 12	4.8	2.2
B075MBT713RK	005943								4	1/4	107											
B100MBT713XK	008562	100	4.17/0.87	3	5/8	92	3	3/4	95	3	3/16	81	2	7/16	61	3	1/8	79	.203 X .460	5 X 12	5.9	2.7
B100MBT713RK	008531								4	9/16	115											
B150MBT713XKF	048117	150	6.25/1.30	4	1/4	108	3	3/4	95	3	3/16	81	3	3/16	81	3	1/8	79	.203 X .460	5 X 12	8.0	3.6
B150MBT713RKF	048155								4	9/16	115											
B200MBT713XKF	048148	200	8.33/1.74	4	1/4	108	4	1/2	114	3	7/8	99	3		76	3	3/4	95	.203 X .460	5 X 12	9.0	4.1
B200MBT713RKF	048162								5	1/4	133											
B250MBT713XKF	047929	250	10.42/2.17	4	3/4	121	4	1/2	114	3	7/8	99	3	3/4	95	3	3/4	95	.203 X .460	5 X 12	12.0	5.5
B250MBT713RKF	048209								5	1/4	133											
B300MBT713XKF	047967	300	12.50/2.61	5	3/16	132	5	1/4	133	4	1/2	114	3	7/8	99	4	3/8	111	.313 X 1.063	8 X 27	14.0	6.4
B300MBT713RKF	048124								5	7/8	148											
B350MBT713XKF	047905	350	14.58/3.04	5	3/16	132	5	1/4	133	4	1/2	114	3	7/8	99	4	3/8	111	.313 X 1.063	8 X 27	15.0	6.8
B350MBT713RKF	048216								5	7/8	148											
B500MBT713XKF	048193	500	20.84/4.35	6	11/16	170	5	1/4	133	4	1/2	114	5	3/8	137	4	3/8	111	.313 X 1.063	8 X 27	18.0	8.2
B500MBT713RKF	048261								5	7/8	148											

NOTE: RK, RKF SUFFIX = PRIMARY CL "CC" FUSE BLOCK ATTACHED. DIMENSION "C" CHANGE NOTED.