

MEF EMC-FILTER 1-PHASE 1-STAGE

I:20A U:250 VAC/300 VDC snap on

Current: 20 A
DIN-rail mountable
for universal applications
Attenuation curves on request.

[Link to Product](#)

Illustration

Test isolation voltage	2.7 kV (L-N) 2 s; 2 kV (L-L) 2 s (EN 60939-2)
Connection	Screw connection touch protected
Mounting method	DIN rail mountable TH35 (EN 60715)
Dimensions H×W×D	07×65×39 mm

Technical Data

Operating voltage	max 250 V AC/300 V DC
Operating frequency	50-60 Hz
Overload current	8× (N t) max 0.5 ms; 5× (N t) max min (× per hour)
Consumption	max 5 mA (250 V AC)
Connection cross section	0.2-6 mm ² single core (AWG 24-9); 0.2-4 mm ² multiple core (AWG 24-)

Commercial data

country of origin	T
customs tariff number	85363030
EAN	404887902939
eClass	27 30806
Packaging unit	