

**MODLINK MSDD DATA INSERT**

1×SUB-D9 female/female Profi bus interface

SUB-D9

1× SUB-D9 (blind plug)

1× SUB-D9 (female) PROFIBUS

**Illustration**

Product may differ from Image

**General data**

Dimensions H×W×D	88×51×40 mm
------------------	-------------

**SUB-D9**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

**Commercial data**

country of origin	CZ
customs tariff number	85366990
EAN	4048879301947
eClass	27189217
Packaging unit	1