

**MODLINK MSDD SINGLE COMBI INSERT GREAT BRITAIN**

1x RJ45 + 1x data cutout

1x Great Britain (BS)

1x RJ45, 8-pole metal, CAT6A (female/female)

1x RJ45 cut-out

**Illustration**

Product may differ from Image

**General data**

Protection	IP20
Dimensions H×W×D	87.5×50.7×43 mm (3.44×1.99×1.69 in)
Temperature range	-5...+50 °C
Storage temperature range	-10...+60 °C (14...140 °F)

**RJ45**

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT6A

**Shielding plate**

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

**England (BS)**

Operating voltage	250 V AC
Operating current	13 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm <sup>2</sup> (AWG 12)

**Commercial data**

country of origin	LV
customs tariff number	85366990
EAN	4048879601023
eClass	27189217

Packaging unit

1