

**Modlink MSDD-set: Frame 4000-68223-000000,**  
insert 4000-68000-0030000 + 4000-68000-0410000

### Illustration



Product may differ from Image

### Frame

suitable for mounting with wall thickness 1...5 mm

Protection IP65

Housing Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

**SUB-D25**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	25-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

**SUB-D9**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

**USA**

Operating voltage	125 V AC
Operating current	15 A
No. of poles	2 + PE
Connection	Plug-solder connection: 4.8×0.5 mm

**Commercial data**

country of origin	CZ
customs tariff number	85389099
EAN	4048879033053
eClass	27189217
Packaging unit	1