

Modlink MSDD-set: Frame 4000-68223-000000,
insert 4000-68000-0040000 + 4000-68000-0310000

Illustration



Product may differ from Image

Frame

suitable for mounting with wall thickness 1...5 mm

Protection IP65

Housing Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

SUB-D15 HD

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current (UL Rating) max. 175 mA

No. of poles 15-pole

Connection front side SUB-D (female)

Connection rear side SUB-D (solder connection)

Locking of ports UNC 4...40 bolt

SUB-D9

Operating voltage 48 V AC/DC

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current 3 A

Operating current (UL Rating) max. 175 mA

No. of poles 9-pole

Connection front side SUB-D (female)

Connection rear side SUB-D (solder connection)

Locking of ports UNC 4...40 bolt

USA

Operating voltage 125 V AC

Operating current 15 A

No. of poles 2 + PE

Connection Screw terminals: max. 2× 2.5 mm² (AWG 14)

Commercial data

country of origin CZ

customs tariff number 85389099

EAN 4048879033015

eClass 27189217

Packaging unit 1