

Modlink MSDD-set: Frame 4000-68522-0000001,

insert 4000-68000-4310003

Illustration



Product may differ from Image

Frame

suitable for mounting with wall thickness 1...5 mm

Protection IP65

Housing Frame: plastic PA black, cap: plastic PC transparent

Temperature range -30...+70 °C (storage temperature -30...+80 °C)

RJ45

| | |
|-------------------------------|---------------------------------------|
| Operating voltage (UL Rating) | max. 30 V AC/42.4 V DC |
| Operating current (UL Rating) | max. 175 mA |
| Connection front side | RJ45 |
| Connection rear side | RJ45 |
| Locking of ports | Snap In |
| Specification | CAT5e, Class D, 100 MHz, (EN 50173-1) |

Shielding plate

| | |
|-------------------|------------------|
| Connection | Threaded hole M4 |
| Tightening torque | 0.9 Nm ±0.1 |

USB

| | |
|-------------------------------|--------------------------|
| Operating voltage | 48 V AC/DC |
| Operating voltage (UL Rating) | max. 30 V AC/42.4 V DC |
| Operating current | 1.5 A |
| Locking of ports | Snap In |
| Specification | USB: 3.0 (max. 5 Gbit/s) |

France (UTE-NF)

| | |
|-------------------|---|
| Operating voltage | 250 V AC |
| Operating current | 16 A |
| No. of poles | 2 + PE |
| Connection | Screw terminals: max. 2× 4 mm ² (AWG 12) |

Commercial data

| | |
|-----------------------|---------------|
| country of origin | DE |
| customs tariff number | 85366990 |
| EAN | 4048879445900 |
| eClass | 27189217 |
| Packaging unit | 1 |