





**MIRO 6.2 230V-1U OUTPUT RELAY**

IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A

1 NO/NC contact  
6 A  
230 V AC/DC  
Screw terminals

**Illustration**



Product may differ from Image

### Approvals



### Input

Connection voltage - current	230 V AC/DC (195...253 V AC/DC) - 3 mA
LED display	LED (green)

### Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 6 A
Min. load current	10 mA (12 V DC)
Power rating (voltage dependent)	max. 1500 VA/120 W
Switching frequency	max. 10 Hz
Contact material	Ag Sn O2
Energize/release/contact bounce time	10/15/1.5 ms

### Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)

### General data

Mech./ elect. life	20 000 000 switching cycles/load dependent
Test isolation voltage	4 kV; safe separation (EN 60947-1)
Mounting method	DIN-rail mountable (EN 60715)

Temperature range	-20...+55 °C
Dimensions H×W×D	91 ×6.2×70 mm

**Commercial data**

country of origin	CZ
customs tariff number	85364900
EAN	4048879027175
eClass	27371001
Packaging unit	1