

MASI67 I/O MODULE

4 digital inputs

Digital inputs

DI4 - 0.2 A (AB) - 4× M8

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.

Illustration

Product may differ from Image

Approvals**Input**

| | |
|------------------|----------------------------------------------------------------------|
| Type | for 3-wire sensors or mechanical switches, PNP |
| Sensor supply US | max. 200 mA from AS-Interface (short-circuit and overload protected) |

General data

| | |
|-------------------|-------------------------------------------------|
| Protection | IP67 |
| Mounting method | DIN-rail mountable (EN 60715) or screw fixing |
| Temperature range | -20...+60 °C (storage temperature -20...+70 °C) |
| Dimensions H×W×D | 94×60×39 mm |

Technical Data

| | |
|------------------------------|-------------------------------------|
| Bus voltage (AS-Interface) | 26.5...31.6 V DC |
| Total current (AS-Interface) | max. 250 mA |
| Addressing | via built-in address port or master |
| Address range | 1...62 (1...31 A or B) |
| Profile (IO/ID/ID2 code) | S-0.A.0 |

Diagnostic

| | |
|-------------------------|------------|
| Communication status | via LED |
| Diagnostic via LED | per module |
| Monitoring - no voltage | yes |

Commercial data

| | |
|-----------------------|---------------|
| country of origin | DE |
| customs tariff number | 85176200 |
| EAN | 4048879049061 |
| eClass | 27242604 |
| Packaging unit | 1 |