


**IMPACT20 PROFIBUS, DIGITAL IN-/OUTPUT MODULE**

8 digital inputs and 8 digital outputs

Digital inputs/outputs

DI8 DO8 - 2 A

Connection cables are in the online shop under "Connection Technology".

**Illustration**

Product may differ from Image

**Approvals****More Info****Input**

Sensor supply US

24 V DC (EN 61131-2), max. 700 mA per module, short-circuit and overload protected

Type for 3-wire sensors or mechanical switches, PNP

#### Output

Switching current per output	max. 2 A (short-circuit and overload protected)
Total current	max. 8 A

#### Connections

Fieldbus	PROFIBUS 12 Mbit/s; SUB-D9
Sensor-system/actuator supply	6× spring clamp plug-in terminals, max. 2.5 mm <sup>2</sup> (max. 12 A)
I/O ports	18× spring clamp plug-in terminals, max. 2.5 mm <sup>2</sup> (max. 12 A)

#### General data

Protection	IP20
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+55 °C (storage temperature -20...+70 °C)
Dimensions H×W×D	117×56×47 mm

#### Module supply

Operating voltage	24 V DC (EN 61131-2)
-------------------	----------------------

#### PROFIBUS

Addressing	Rotary switch 3...99
------------	----------------------

#### Diagnostic

Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module and channel
Monitoring - under voltage	yes
Monitoring - no voltage	yes
Short-circuit and overload	yes

#### Commercial data

country of origin	DE
customs tariff number	85389099
EAN	4048879048095
eClass	27242604
Packaging unit	1