


## TREE 8TX METALL - UNMANAGED SWITCH - 8 PORTS

8 port unmanaged switch


Connection cables are in the online shop under "Connection Technology".

### Illustration



Product may differ from Image

### Approvals



### Connections

Fieldbus	8× RJ45
Supply	Screw plug-in terminal: 0.2...1.5 mm <sup>2</sup>

### General data

Protection	IP50
Housing	Metal black
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-10...+70 °C (storage temperature -40...+85 °C)
Dimensions H×W×D	90×45.2×78 mm

### Technical Data

Operating voltage	2× 9...48 V DC, redundancy
Transfer rate	10/100 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

**Switch Management**

Switch Form	Unmanaged Switch
Websserver	no
VLAN (QoS) IEEE 802.p	yes
Port Mirroring	no
Protocols	no
Remote maintenance	no
Alarm contact	no

**Diagnostic**

Communication status	via LED
Monitoring - no voltage	yes

**Commercial data**

country of origin	TW
customs tariff number	85176200
EAN	4048879329576
eClass	19170106
Packaging unit	1