


Xelity 8TX Unmanaged Switch 8 Port 100Mbit

8 port unmanaged switch


Connection cables are in the online shop under "Connection Technology".

Illustration



Product may differ from Image

Approvals



Connections

Fieldbus	8× RJ45
Supply	Push-In spring clamp terminals, 0.2...2.5 mm ² (0.25...1.5 mm ²)

General data

Protection	IP20
Housing	Black plastic
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-25...+60 °C (storage temperature -40...+85 °C)
Dimensions H×W×D	105×41.6×85.1 mm

Technical Data

Operating voltage	9.5...31.5 V
Transfer rate	10/100 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

Switch Management

Switch Form	Unmanaged Switch
Webserver	no
VLAN (QoS) IEEE 802.p	yes
Port Mirroring	no
Protocols	no
Remote maintenance	no
Alarm contact	no

Diagnostic

Communication status	via LED
Monitoring - no voltage	yes

Commercial data

country of origin	DE
customs tariff number	85176200
EAN	4048879798808
eClass	19170106
Packaging unit	1