



MIRO TR 24VDC FK OPTO-COUPLER MODULE

IN: 48 VDC - OUT: 48 VDC / 2 A

Transistor 2 A
24 V DC
Spring clamp terminals

Illustration

Product may differ from Image

Approvals

**Input**

Voltage range ON	10...48 V DC
Voltage range OFF	0...5 V DC
Control current	6 mA
LED display	LED (yellow)

Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...2 A
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 10 μ A
Switching time ON/OFF	1/5 ms
Switching frequency	max. 10/1 Hz (resist./ind.)

General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H×W×D	78×6.2×70 mm

Commercial data

country of origin	CZ
customs tariff number	85414090
EAN	4048879021876
eClass	27371601
Packaging unit	1