

**M12 FEMALE 0° SELF WIREABLE SCREW TERMINAL**5-pol. 0,14 - 1,5mm<sup>2</sup>, 2,5-8mm cable diameter

Female straight

M12, 5-pole


Screw terminals

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

**Illustration**

Female



Product may differ from Image

**Approvals****Form**

Form 12931

**General data**

Temperature range -30...+85 °C

Dimensions H×W×D 57×20×20 mm

**Technical Data**



Operating voltage max. 60 V AC/DC

Operating current per contact max. 7.5 A (+40 °C; 1.5 mm<sup>2</sup>)Connection cross section max. 1.5 mm<sup>2</sup>

Sealing range (cable Ø)	2.5...8.0 mm
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm
Protection	IP67 inserted and tightened (EN 60529)

**Commercial data**

country of origin	CZ
customs tariff number	85366990
EAN	4048879438230
eClass	27279221
Packaging unit	1

**Sketch**

Product may differ from Image