

M12 FEMALE 0° FIELD-WIREABLE

Female straight


M12, 4-pole

Screw terminals

Sealing range (cable Ø): 8...10 mm

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Illustration

Product may differ from Image

Form

Form 12945

Technical Data

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 8 A
Connection cross section	max. 1.5 mm ²
Sealing range (cable Ø)	8...10 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range -25...+85 °C


Commercial data

country of origin	DE
customs tariff number	85366990

EAN	4048879378369
eClass	27279221
Packaging unit	1

Sketch

Female



Product may differ from Image