

MOSA M12 FEMALE 0° FIELD-WIREABLE (IDC)B-cod., 3-pol., 0,25-0,34mm², shielded

Female straight

M12, 3-pole

B-coded

shielded

IDC terminals

Sealing range (cable Ø): 7...8.8 mm

Illustration

Product may differ from Image

Approvals**Form**

Form 14221

Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.34 mm ² (AWG 22...24)
Sealing range (cable Ø)	7.0...8.8 mm
Outer wire Ø	2.0...2.6 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range -25...+85 °C

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879197700
eClass	27279221
Packaging unit	1