

M16 MALE, 0° 14 POLE,

PUR 8x0.25 + 2x0,5 black 2m

Male straight
M16, 14-pole
partly used
with cable sleeves
Further cable lengths on request.

Illustration

Product may differ from Image

Form

Form 16751

Cables

Cable number	959
No./diameter of wires	8 x 0.25 + 2 x 0.5 mm ²
Wire isolation	PVC (wh, gn, ye, gr, grpk, rdbl, whgn, brgn; br, bl)
Jacket Color	black
Material (jacket)	PUR/PVC
Outer Ø	8.0 mm ±5%
Bend radius (moving)	15 x outer Ø
Temperature range (fixed)	-25...+70 °C
Temperature range (mobile)	-5...+70 °C

Technical Data

Operating voltage	max. 24 V AC/DC
Operating current per contact	max. 3 A
Protection	IP66K, IP67 inserted and tightened (EN 60529)

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879196727
eClass	27279218
Packaging unit	1