

M23 FEMALE, 90° 19 POLE

PUR 12x0.34+3X0.75 GRAY, drag ch 5m

Female 90°

M23, 19-pole


15-pole used

with cable sleeves


Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Form

Form 23331

Cables

Cable number 388

No./diameter of wires 12× 0.34 + 3× 0.75 mm²

Wire isolation PVC (yebr, rd, grpk, wh, rdbl, gn, whgn, ye, brgn, gr, whye, pk, br, gnye, bl)

C-track properties 2 Mio.

Jacket Color gray

Material (jacket) PUR/PVC

Outer Ø 9.8 mm ±5%

Bend radius (fixed) 10× outer Ø

Bend radius (moving) 12× outer Ø

Temperature range (fixed) -30...+80 °C

Temperature range (mobile)	-5...+70 °C
Color (jacket)	gray

Technical Data

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 7.5 A
Locking of ports	Screw thread (M23×1 mm) recommended torque 2.0 Nm, self-securing
Protection	IP67 inserted and tightened (EN 60529)
Compression gland	M23 (SW27)

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879187909
eClass	27279218
Packaging unit	1