

M23 female 0° with cable shielded

PUR 8x0.34+3x0.75 shielded gy UL/CSA+drag ch. 10m

Female straight

M23, 19-pole

11-pole used


for 4-way distribution boxes, 5-pole

Shield on M23 cap nut


Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Form

Form 23711

General data

Temperature range -25...+85 °C, depending on cable quality

Cables

Cable number	373
No./diameter of wires	8 × 0.34 + 3 × 0.75 mm ²
Wire isolation	TPE (grpk, wh, rdbl, gn, whgn, ye, brgn, gr, br, bl, gnye)
C-track properties	5 Mio.
Jacket Color	gray
Material (jacket)	PUR (UL/CSA)
Outer Ø	9.3 mm ±5%
Bend radius (fixed)	10 × outer Ø
Bend radius (moving)	12 × outer Ø
Temperature range (fixed)	-40...+90 °C
Temperature range (mobile)	-40...+90 °C

Shield	yes
Color (jacket)	gray

Technical Data

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 7.5 A
Locking of ports	Screw thread (M23×1 mm) recommended torque 2.0 Nm, self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Compression gland	M23 (SW27)

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879187763
eClass	27279218
Packaging unit	1