

DESINA HYBRIDFIELDBUS

PUR 2x0.34 + 4x1,5 violet 15m

DESINA® ECOFAST®

Male straight – female straight

6-pole, CU


shielded

Further cable lengths on request.

Han-Brid ® a registered trademark of HARTING KGaA.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 33011

General data

Temperature range -25...+85 °C, depending on cable quality

Cables

Cable number	964
No./diameter of wires	4 × 1.5 + 2 × 0.34 mm ²
Wire isolation	PVC (bk num), (rd, gn)
Jacket Color	violet
Material (jacket)	PUR
Outer Ø	10.0 mm ±5%
Bend radius (moving)	8 × outer Ø
Temperature range (fixed)	-30...+70 °C
Temperature range (mobile)	-40...+60 °C

Technical Data

Operating voltage	max. 24 V AC/DC
Operating current per contact	max. 10 A
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	Clip locking

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879186773
eClass	27279218
Packaging unit	1