

T-coupler SlimLine M12-male 5p./ 2x M12-female 3p.

T-coupler (Slim Line)

Male straight – females straight

M12 – M12, 5-pole

Distribution function (NO)

Safety

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Illustration

Product may differ from Image

Approvals

* only for products with UL/CSA approved cable

Form

Form 41155

Technical Data

Operating voltage max. 60 V AC/DC

Operating voltage (only UL listed) max. 30 V DC

Operating current per contact max. 4 A

Locking of ports Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing

Protection IP65 and IP67 when plugged and screwed down (EN 60529)

Rated surge voltage 0.8 kV

General data

Temperature range -25...+85 °C

Commercial data

country of origin DE

customs tariff number 85366990

EAN 4048879404167

eClass 27143423

Packaging unit 1

Sketch

