

7/8" MALE 0° FIELD-WIREABLE SCREW

4-pol. clamp section 6-8 mm

Male straight

7/8" (4-pole)

Screw terminals

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**General data**

Temperature range -25...+85 °C

Technical Data

Operating voltage max. 300 V AC/DC

Operating current per contact max. 9 A

Connection cross section max. 1.5 mm²

Sealing range (cable Ø) 6...8 mm

Locking of ports Screw thread 7/8" (recommended torque 1.5 Nm) self-securing

Protection IP67 inserted and tightened (EN 60529)

Commercial data

country of origin DE


customs tariff number 85366990

EAN 4048879134798

eClass 27279218

Packaging unit 1

Sketch



Product may differ from Image