

M8 ADAPTOR ON REAR OF MSUD VALVE PLUG FORM A 18MM

LED 24 V AC/DC

Form A (18 mm) – M8, connector at the rear

24 V AC/DC $\pm 25\%$

LED

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Form**

Form 88913

General data

Temperature range -25...+85 °C

Technical Data

Operating voltage	24 V AC/DC $\pm 25\%$
Operating current per contact	max. 4 A
Configuration	2 contacts + bridged PE
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3/M8 (recommended torque 0.4 Nm)
Rated surge voltage	0.8 kV

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879115988

eClass 27143423

Packaging unit 1