

M8 ADAPTOR ON TOP / MSUD VALVE PLUG FORM C 8MM

Adapter

Form C (8 mm) – M8, connector top entry

24 V AC $\pm 20\%$ / DC $\pm 25\%$

LED and suppression

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 88965

General data

Temperature range -25...+85 °C

Technical Data

Operating voltage 24 V AC $\pm 20\%$ / DC $\pm 25\%$

Operating current per contact max. 4 A

Current consumption max. 15 mA

Switch off peak max. 55 V

Configuration 2 contacts + bridged PE

Locking of ports M3/M8 (recommended torque 0.4 Nm)

Protection IP67 inserted and tightened (EN 60529)

Rated surge voltage 0.8 kV

Commercial data

country of origin CZ

customs tariff number	85366990
EAN	4048879347426
eClass	27143423
Packaging unit	1