

M12/D-SUB PROFIBUS ADAPTER 35°

M12 male B-cod./M12 female B-cod.

PROFIBUS

Bus connection plug 35°

SUB-D9 (male); M12× 1 mm, B-coded

Programming device

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 99401

General data

Dimensions H×W×D 68×42×17 mm

Temperature range -20...+70 °C

Technical Data

Operating voltage 4.75...5.25 V DC (via the fieldbus device)

Current consumption max. 12.5 mA

Transfer rate max. 12 Mbit/s

Connection M12×1 mm

Terminating resistor integrated, switchable

Protection IP30

Commercial data

country of origin HU

customs tariff number 85366990

EAN 4048879303620

eClass 27061801

Packaging unit 1