

M12 FEMALE FLANGE PLUG A CODED FRONT MOUNT F&B

PP-wires 8x0,25 0.5m


F&B

Flange female


M12, 8-pole

Front mounting

Stainless steel 1.4404 (V4A)

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Approvals**Form**

Form 17181

General data

Pollution Degree 3

Temperature range -25...+85 °C

Cables

Cable number	973
No./diameter of wires	8 × 0.25 mm ²
Wire isolation	PUR (wh, br, gn, ye, gr, pk, bl, rd)
Outer Ø	1.25 mm ±5%
Bend radius (fixed)	10 × outer Ø
Temperature range (fixed)	-40...+90 °C
Temperature range (mobile)	-25...+90 °C

Technical Data

Operating voltage	max. 30 V AC/DC
Rated surge voltage	0.8 kV
Operating current per contact	max. 2 A
No. of poles	8
Material group	IEC 60664-1, category I
Coding	A-coded
LED display	no
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Compression gland	M12 (SW14)
Protection	IP67 inserted and tightened (EN 60529)
Protection NEMA	3, 4, 6P (UL 50E)
Locking material	Stainless steel 1.4404 (V4A)

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879364348
eClass	27279220
Packaging unit	1

Sketch

1	white
2	brown
3	green
4	yellow
5	gray
6	pink
7	blue
8	red

Product may differ from Image