

Valve plug SuperSeal female 4-pol. with cable

PUR 4x0.75 bk 10m

Xtreme - Outdoor

Male straight

max. 24 V DC

4-pole

without components

without cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 73161

General data

| | |
|----------------------------|-------------------------------------------|
| Mounting method | inserted |
| Material (contact) | Copper alloy |
| Material (contact surface) | Sn |
| Material (gasket) | Silicon |
| Pollution Degree | 3 |
| Temperature range | -40...+125 °C, depending on cable quality |

Cables

| | |
|-----------------------|--------------------------|
| Cable number | 514 |
| No./diameter of wires | 4 x 0.75 mm ² |
| Wire isolation | PP (br, wh, bl, bk) |
| C-track properties | 2 Mio. |

| | |
|----------------------------|------------------------------------------|
| Jacket Color | black |
| Material (jacket) | PUR (UL) |
| Outer Ø | 5.7 mm ±5% |
| Bend radius (moving) | 6 × outer Ø |
| Temperature range (mobile) | -25...+80 °C |
| Cable identification | 514 |
| Material (wire) | Cu wire, bare |
| Resistor (core) | max. 58 Ω/km (20 °C) |
| Construction (core) | 42 × 0.15 mm (multi-strand wire class 6) |
| Diameter (core) | 4 × 0.75 mm ² |
| AWG | similar to AWG 18 |
| Material (wire isolation) | PP |
| Wire-Ø incl. isolation | 1.79 mm ±5% |
| Color/numbering of wires | br, bk, bl, wh |
| Stranding combination | 4 wires twisted |
| Shield | no |
| Material (jacket) | PUR |
| Outer-Ø (jacket) | 5.7 mm ±5% |
| Color (jacket) | black |
| Nominal voltage | 300 V |
| Temperature range (mobile) | -25...+80 °C |
| Bend radius (moving) | 6 × outer Ø |

Technical Data

| | |
|-------------------------------------------|----------------------------------------|
| Operating voltage | max. 24 V DC |
| Rated surge voltage | 1.5 kV |
| Operating current per contact | max. 7 A |
| No. of poles | 4-pole |
| LED display | no |
| Locking of ports | Snap-in connector |
| Protection | IP67 inserted and tightened (EN 60529) |
| Material | PUR |
| suitable for corrugated tube (internal Ø) | 11 mm |
| Housing | AMP SuperSeal 1.5, black plastic |
| Additional suppressor | without components |

Commercial data

| | |
|-----------------------|---------------|
| country of origin | DE |
| customs tariff number | 85444290 |
| EAN | 4048879682497 |
| eClass | 27279218 |
| Packaging unit | 1 |