

Valve plug SuperSeal male 3-pol. with cable

PUR 3x0.75 bk 10m

Xtreme - Outdoor

Female straight

max. 24 V DC

3-pole

without components

without cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 73381

General data

Mounting method	inserted
Temperature range	-40...+125 °C, depending on cable quality
Material (gasket)	Silicon
Material (contact)	Copper alloy
Material (contact surface)	Sn
Pollution Degree	3

Cables

Cable number	513
No./diameter of wires	3 x 0.75 mm ²
Wire isolation	PP (br, bl, bk)
C-track properties	4 Mio.
Jacket Color	black
Material (jacket)	PUR (UL)
Outer Ø	5.3 mm ±5%
Bend radius (moving)	10 x outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

Technical Data

Operating voltage	max. 24 V DC
Rated surge voltage	1.5 kV
Operating current per contact	max. 8 A
No. of poles	3-pole
LED display	no
Locking of ports	Snap-in connector

Protection	IP67 inserted and tightened (EN 60529)
Material	PUR
suitable for corrugated tube (internal Ø)	11 mm
Housing	AMP SuperSeal 1.5, black plastic
Additional suppressor	without components

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879682633
eClass	27279218
Packaging unit	1