

Mini (7/8) 4 pole, Male (Ext.) Straight/Female Straight

PUR, UL/CSA, 4x16AWG, black, 1.5m

Male straight – female straight

7/8" – 7/8", 4-pole



Power cable

USA

Further cable lengths on request.


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Male

Female



Product may differ from Image

Approvals



* only for products with UL/CSA approved cable

Form

Form A4A01

General data

Temperature range -25...+80 °C, depending on cable quality

Cables


Cable number	UMC
No./diameter of wires	4 × 1.5 mm ²
Construction (core)	2.3 mm ±5%
Wire isolation	TPM (br, wh, bl, bk)
C-track properties	5 Mio.
Jacket Color	black
Material (jacket)	PUR (UL/CSA)
Outer Ø	8.0 mm ±5%
Bend radius (fixed)	7.5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-50...+80 °C
Temperature range (mobile)	-20...+80 °C

Technical Data

Operating voltage	max. 600 V AC/DC
Operating current per contact	max. 9 A
Locking of ports	Screw thread 7/8" (recommended torque 1.5 Nm) self-securing
Compression gland	7/8" (SW24)
Protection	IP68 inserted and tightened (EN 60529)
Locking material	Zinc die casting, matte nickel plated
Material	PUR

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879698115
eClass	27279218
Packaging unit	1

Sketch

Product may differ from Image