

**MEN POWER SUPPLY 1/2-PHASE, SMOOTHED**

IN: 230/400±15VAC OUT: :24V/5ADC

Current: 5 A

Output rating: 120 W

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals****Input**

Input voltage	230/400 ±15 V AC
Input fuse (external)	1.6 AT (230 V AC); 1.0 AT (400 V AC)
Frequency	50...60 Hz
Input current	0.97 A (230 V AC); 0.56 A (400 V AC)

**Output**

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 5 A (230 V AC); 6 A (400 V AC)
Ripple	max. 5% eff/rms
Output fuse	10 A (automotive fuse FKS)
Output suppression	LED, VDR and smoothing capacitor



**General data**

Standards	EN 61558-2-6, EN 62041 category I, EN 55011 B, EN 61000-3-2
Mounting method	Key-hole mounting
Dimensions H×W×D	95×96×136 mm
Fixing centers a×b×c	75×84×5.8 mm
Temperature range	-20...+60 °C, no condensation

**Commercial data**

country of origin	CZ
customs tariff number	85044090
EAN	4048879080064
eClass	27049002
Packaging unit	1

### Sketch



Product may differ from Image