


MKN POWER SUPPLY 1-PHASE, LINEAR REGULATED

IN: 230VAC OUT: 2x15V/0,06ADC

INPUT: 230 V AC
 OUTPUT: +-15 V DC
 Current: 2× 35 mA

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

[Link to Product](#)**Illustration**

Product may differ from Image

Input

Input current	approx. 20 mA
Input fuse (external)	63 mA (T)
Frequency	50...60 Hz

Output

Output current	max. 2× 35 mA
Output suppression	LED, VDR and smoothing capacitor
Ripple	max. 10 mV ss/pp
Unit protection	short-circuit and overload protected
LED display	LED (green): in operation

General data

Standards	EN 61558-2-6, EN 62041 category II, EN 55011 B, EN 61000-3-2
Temperature range	0...+60 °C, no condensation
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)

Commercial data

country of origin	CZ
customs tariff number	85044090
EAN	4048879079631
eClass	27049002
Packaging unit	1