


MDD DC/DC-CONVERTOR SWITCH MODE

IN: 24VDC OUT: 24V/0,3ADC

INPUT: 24 V DC
 OUTPUT: 24 V DC
 Output rating: 7 W
 Current: 0.3 A

[Link to Product](#)**Illustration**

Product may differ from Image

Input

Input voltage	24 V DC
Input current	0.6 A
Input fuse (external)	2 A (T)
Input fuse (internal)	1.5 A (T)

Output


Output fuse	short-circuit and overload protected, restart after overload by removing power supply
Output voltage	24 V DC (SELV), $\pm 2\%$
Output current	max. 0.3 A
Ripple	max. 0.2% eff/rms

General data

Standards	EN 61204-3
Test isolation voltage	4 kV (input/output)
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	0...+50 °C, no condensation

Commercial data

country of origin	CZ
customs tariff number	85043121
EAN	4048879079556
eClass	27210901
Packaging unit	1

Sketch

Product may differ from image