

MPL POWER SUPPLY 3-PHASE, SMOOTHED

IN: 400VAC+/- 5% OUT: 24V/30ADC

Current: 30 A

Output rating: 720 W

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Input**

Input voltage	3 × 400 V AC ±5%
Input current	1.6 A (3 × 400 V AC)
Input fuse (external)	2 A (T)
Frequency	50...60 Hz

Output

Output voltage	24 V DC (SELV)
Output current	max. 30 A
Ripple	max. 2% eff/rms
Output fuse external	30 A T
Output suppression	LED, VDR and smoothing capacitor

General data



Standards	EN 61558-2-6, EN 62041 category I, EN 55011 B, EN 61000-3-2
Temperature range	-20...+55 °C, for any mounting position at vertical wall, no condensation
Mounting method	Key-hole mounting
Efficiency	76%
Dimensions H×W×D	240×107×250 mm
Fixing centers a×b×c	215×87×8.5 mm

Commercial data

country of origin	CZ
-------------------	----

customs tariff number	85044090
EAN	4048879079198
eClass	27049002
Packaging unit	1

Sketch



Product may differ from Image