

## MST 1-PHASE CONTROL AND ISOLATION TRANSFORMER

P: 2000VA IN: 208...550VAC OUT: 2x115VAC

Single-phase - Control and Isolation Transformers  
2000 VA  
Isolation class T 40/B  
Other voltages on request.

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Input

Input voltage	208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 V AC
Input current	10.2 A (208 V AC); 3.86 A (550 V AC)
Inrush current	179 A (208 V AC); 68 A (550 V AC)
Short-circuit current	473 A (208 V AC); 180 A (550 V AC)
Frequency	50...60 Hz

#### Output



Output voltage	1 × 230, 1 × 115, 2 × 115 V AC
Output rating	2000 VA

#### General data

Standards	EN 61558-1, EN 61558-2-4, EN 62041 category 0
Test isolation voltage	4 kV (prim./sec.)
Mounting method	Key-hole mounting
Dimensions H×W×D	185×192×185 mm
Fixing centers a×b×c	155×150×10 mm
Drill hole Ø	10×18 mm
Temperature range	-20...+40 °C (storage temperature -40...+80 °C)

**Commercial data**

country of origin	CZ
customs tariff number	85043200
EAN	4048879078702
eClass	27031302
Packaging unit	1

**Sketch**

Product may differ from Image