

MTS 1-PHASE CONTROL AND ISOLATION TRANSFORMER


P: 63VA IN: 230/400VAC +/- 15VAC OUT: 230VAC

Single-phase - Control and Isolation Transformers

63 VA

Isolation class T 40/B

Other voltages on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Input**

Input voltage	230/400 ±15 V AC
Frequency	50...60 Hz
Input current	0.32 A (230 V AC); 0.18 A (400 V AC)
Inrush current	2 A (230 V AC); 1.15 A (400 V AC)
Short-circuit current	2.64 A (230 V AC); 1.52 A (400 V AC)

Output

Output voltage	230 V AC
Output rating	63 VA



General data

Standards	EN 61558-1, EN 61558-2-4, EN 62041 category 0
Test isolation voltage	4 kV (prim./sec.)
Mounting method	Long-hole mounting or DIN-rail mountable TH35 (EN 60715)
Temperature range	-20...+40 °C (storage temperature -40...+80 °C)
Drill hole Ø	4.8×8.4 mm
Dimensions H×W×D	79×78×93 mm
Fixing centers a×b×c	56×56×4.8 mm

Commercial data

country of origin	CZ
customs tariff number	85043180
EAN	4048879078399
eClass	27031302
Packaging unit	1

Sketch



Product may differ from Image