

SCREW PLUG M12 METAL

Screw plug M12×1 mm
 Metal, hex, 1 piece

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form	996049
------	--------

General data

Temperature range	-100...+205 °C
-------------------	----------------

Technical Data

Protection	IP65, IP66K, IP67, IP68, IP69K inserted and tightened (EN 60529)
------------	--

Material	Brass, nickel plated
----------	----------------------

Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
------------------	--

Commercial data

country of origin	DE
-------------------	----

customs tariff number	74153300
-----------------------	----------

EAN	4048879058780
-----	---------------

eClass	23111190
--------	----------

Packaging unit	1
----------------	---