



Cable entry plate plastic type KDP/N 24



PRODUCT INFORMATION

2nd generation of our cable entry plates, plastic, square, with improved clip-in function.

Economical connection technology for tool-free wiring of equipment and machinery. Wherever the rapid and economical introduction of cables and/or pneumatic hoses in confined spaces is essential. The alternative to cable fittings. Suitable for standard cut-

outs for 24-pin Harting and Wieland plug connectors. For snap-in fastening and/or screwing in place.

- Snap-in at plate thicknesses of 1.5 to 2.0 mm
- High degree of strain relief
- 2 elastomer panels (seals)

SPECIFICATIONS

	Enclosure: Polyamide 6.6 Seal: TPU / NBR / EPDM
	IP 65
	-30 – 70 °C
	
	
	
	

Type	Order No.	Colour	No. Openings	Openings Quantity / Ø mm	Pack qty.
KDP/N 24/10 ¹⁾	87301108	Black	10	2x 3.00 – 6.50	1
				1x 5.00 – 9.20	
				5x 9.00 – 14.00	
				2x 14.00 – 20.00	
KDP/N 24/11	87301110	Black	11	4x 3.00 – 6.50	1
				4x 5.00 – 9.20	
				3x 14.00 – 20.00	
KDP/N 24/12	87301120	Black	12	12x 8.00 – 12.00	1
KDP/N 24/13	87301130	Black	13	2x 3.00 – 5.50	1
				6x 4.10 – 8.10	
				4x 9.00 – 14.00	
				1x 14.00 – 20.00	
KDP/N 24/14	87301140	Black	14	6x 3.00 – 6.50	1
				4x 5.00 – 9.20	
				4x 9.60 – 15.90	
KDP/N 24/17	87301150	Black	17	17x 5.00 – 9.20	1
KDP/N 24/17-1	87301151	Black	17	11x 3.00 – 6.50	1
				1x 4.10 – 8.10	
				5x 8.00 – 12.50	
				2x 8.00 – 12.50	
KDP/N 24/22	87301160	Black	22	16x 3.00 – 6.50	1
				4x 5.00 – 9.20	
				2x 8.00 – 12.50	
KDP/N 24/22	87301161	Black	22	16x 3.00 – 6.50	100
				4x 5.00 – 9.20	
				2x 8.00 – 12.50	

Cable entry plate plastic type KDP/N 24

Type	Order No.	Colour	No. Openings	Openings Quantity / Ø mm	Pack qty.
KDP/N 24/23	87301170	Black	23	23x 4.10 – 8.10	1
KDP/N 24/29	87301180	Black	29	29x 3.00 – 6.50	1
KDP/N 24/29	87301182	Black	29	29x 3.00 – 6.50	100
KDP/N 24/80	87301190	Black	80	78x 1.50 – 2.60	1
				2x 2.50 – 5.00	
¹⁾ no UR approval					

DIMENSION TABLE

Type	Order No.	Installation height mm	A mm	B mm	a mm	b mm	c mm	d mm	e mm
KDP/N 24/10 ¹⁾	87301108	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/11	87301110	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/12	87301120	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/13	87301130	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/14	87301140	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/17	87301150	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/17-1	87301151	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/22	87301160	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/22	87301161	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/23	87301170	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/29	87301180	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/29	87301182	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
KDP/N 24/80	87301190	15.00	59.00	147.00	112.00	36.00	65.00	16.00	5.50
¹⁾ no UR approval									

MATERIAL PROPERTIES



Enclosure: Polyamide 6.6
Seal: TPU / NBR / EPDM

MECHANICAL PROPERTIES



Protection class
IP 65

THERMAL PROPERTIES



Temperature / temperature range
-30 – 70 °C

Cable entry plate plastic type KDP/N 24

APPROVALS AND OPERATING PERMITS



TECHNICAL INFORMATION



CONFORMITY



GENERAL INFORMATION



All details given in our sales material prospectuses and catalogues as well as the information available online are based on our current knowledge of the products described.

The electronic data and files made available by Murrplastik, particularly CAD files are based on our current knowledge of the product described.

A legally binding assurance of certain properties or the suitability for a certain purpose can not be determined from this information.

All information with respect to the chemical and physical properties of Murrplastik products as well as application advice given verbally, in writing or by tests, is given to the best of our knowledge.

This does not free the purchaser of carrying out their own inspections and tests in order to determine the suitability of a product for a specific purpose.

Murrplastik accepts no responsibility for the available information being up-to-date, correct or complete. Neither do we accept responsibility for the quality of this information.

Murrplastik accepts no liability for damage caused as a result of using our products.

Murrplastik reserves the right to make technical changes and improvements through constant further development of products and services.

Our General Terms and Conditions apply.

© Murrplastik Systemtechnik GmbH • prod_57774~20170616~890287~kdh_kdp_n_24