

RTCBI Insulated Round Braid in Coil, Tinned Copper – RTCBI15-10 (503400)



Part Number	RTCBI15-10
Article Number	503400
Material	Copper Polyvinylchloride
Finish	Tinned
Nominal Current	75 A
Cross Section	10 mm ²
Number of Wires	560
Wire Diameter	0.006"
Length	82'
Diameter	0.276"
Unit Weight	0.27 lb
Insulation Thickness	0.04"
Insulation Voltage	450 V
Temperature	158 °F Max
Flammability Rating	UL® 94V-0
Standard Packaging Quantity	25 m
UPC	78285668718
EAN-13	3479775034003

Unit weight is per meter (3.28').

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

Copyright © 2015 ERICO International Corporation. All rights reserved.
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

