

MFBT-2 nVent ERIFLEX Flexibar Manual Bending Tool – MFBT-2 (559145)



- Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation
- Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation
- Long handle to apply force during nVent ERIFLEX Flexibar bending up to 10x120x1/12x100x1
- Two bending radiuses: 4 mm and 8 mm (0.16" and 0.32")
- Allows for adjustment of the bending angle for repetitive bending
- Robust blue aluminum base with three fixing points
- Adjustable length setting for nVent ERIFLEX Flexibar
- Quick nVent ERIFLEX Flexibar locking system with no tools required
- RoHS compliant



Part Number	MFBT-2
Article Number	559145
Material	Steel Aluminum
Conductor Width	4.72"
Bending Radius	0.16" 0.32"
Bending Angle	120° Max
Depth	16.3"
Height	9 1/2"
Width	12.6"
Unit Weight	15.4 lb
Certifications	RoHS
Standard Packaging Quantity	1 pc
UPC	78285686524
EAN-13	3479775591452

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.