


MBJYG Grounding and Bonding Braid, Tinned Copper, Halogen Free – MBJYG25-100-8 (563617)



MBJYG Grounding and Bonding Braids are a reliable and convenient ground solution for applications that require flexibility and durability. Designed with halogen-free and flame retardant yellow green insulation, MBJYG braids are made with tinned copper ground braids and solid palms that are ready to install without any additional cutting, stripping, crimping or punching. MBJYG braids also do not require the addition of tin or crimped lugs and the proprietary manufacturing process helps optimize the electrical contact between each wire and helps eliminate moisture issues in the palms, helping prevent corrosion and extend the useful life of the braid.

- Complete range of earth/ground flexible connections from 6 - 25 mm² (11.84 - 49.33 kcmil) cross section and from 100 - 300 mm (3.937" - 11.811") length
- Integral palm, without tin or crimped lugs for superior electrical contact and tensile strength resistance
- Resistant to vibration and fatigue, reducing maintenance
- Provides weight savings, material savings and lower impedance when compared to similar lugged cables with insulation
- Ready to use out of the box, eliminates the need for cutting, stripping, crimping and punching
- Halogen free and flame retardant yellow green insulation
- Quick and easy to install
- Recommended by the EMC/EMI directives and less impedance than cables
- RoHS compliant



| | |
|-----------------------------|------------------------------|
| Part Number | MBJYG25-100-8 |
| Article Number | 563617 |
| Material | Copper Polyolefin |
| Finish | Tinned |
| Dielectric Strength | 15 kV/mm |
| Flammability Rating | UL® 224 VW-1 |
| Halogen Free Rating | EN 14582 |
| Nominal Voltage, UL/CSA/IEC | 600 V |
| Working Temperature | -67 to 257 °F |
| Complies With | IEC® 60439.1 IEC® 61439.1 |
| Ampacity | 150 A |
| Thickness (T) | 0.059" |
| Cross Section | 49.34 kcmil |
| Length (L) | 3.937" |

| | |
|-----------------------------|---------------|
| Part Number | MBJYG25-100-8 |
| Hole Size (HS) | 0.335" |
| A | 0.866" |
| B | 1.102" |
| Unit Weight | 0.066 lb |
| Certifications | cULus RoHS |
| Standard Packaging Quantity | 10 pc |
| UPC | 78285695170 |
| EAN-13 | 0782856951704 |

IEC is a registered trademark of the International Electrotechnical Commission. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

© 2019 nVent All rights reserved
nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.
All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.