

NEER™ Zinc and Plastic Bushings

NEC:
Listed for Ordinary Locations

NEC/CEC:
Listed for Ordinary Locations

GB: Insulated

Applications

- Used with a locknut to terminate rigid and IMC conduit to a box or enclosure.
- Provides a smooth pulling surface.

Features

- Plastic throat liner prevents damage to wire insulation.
- Insuliner rated at 150 °C (302 °F).

Material/Finish

- Zinc diecast

NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E11853
- NEMA: FB-1



GB-100

PB-D: Insulating

Applications

- Threaded plastic bushings are used at the end of threaded conduit, or conduit connector, to provide smooth well rounded bearing surface for wires or cables as required by the National Electrical Code.

Features

- Temperature rating is 105 °C (221 °F).

Material/Finish

- Gray polypropylene

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14817
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 229356
- NEMA: FB-1
- UL Flammability Rating: V-2



PB-D

Trade Size (Inches)	Dimensions in Millimeters (Inches)		Wire Range	Catalog Number
	Diameter	Height		
1/2	26.4 (1.40)	10.7 (0.42)	4-14	GB-100
3/4	33.5 (1.32)	12.4 (0.49)	4-14	GB-200
1	38.1 (1.50)	12.7 (0.50)	4-14	GB-300
1-1/4	49.5 (1.95)	17.0 (0.67)	1/0-14	GB-400
1-1/2	54.1 (2.13)	16.5 (0.65)	1/0-14	GB-500
2	68.8 (2.71)	18.5 (0.73)	1/0-14	GB-600
2 - 1/2	86.6 (3.41)	23.6 (0.93)	1/0-14	GB-700
3	104.1 (4.10)	25.4 (1.00)	1/0-14	GB-800
3 - 1/2	108.7 (4.28)	19.1 (0.75)	1/0-14	GB-900
4	128.0 (5.04)	25.4 (1.00)	1/0-14	GB-1000

Trade Size (Inches)	Dimensions in Millimeters (Inches)		
	Diameter	Height	Catalog Number
1/2	26.2 (1.03)	9.4 (0.37)	PB-100-D
3/4	32.5 (1.28)	9.9 (0.39)	PB-200-D
1	41.9 (1.65)	12.7 (0.50)	PB-300-D
1-1/4	53.3 (2.10)	12.4 (0.49)	PB-400-D
1-1/2	57.9 (2.28)	12.4 (0.49)	PB-500-D
2	67.6 (2.66)	13.7 (0.54)	PB-600-D
2 - 1/2	84.1 (3.31)	16.0 (0.63)	PB-700-D
3	100.3 (3.95)	17.8 (0.70)	PB-800-D
3 - 1/2	112.0 (4.41)	18.0 (0.71)	PB-900-D
4	125.5 (4.94)	18.5 (0.73)	PB-1000-D
5	162.1 (6.38)	25.4 (1.00)	PB-1100-D
6	190.5 (7.50)	25.1 (0.99)	PB-1200-D