

PVC-Coated Conduit Bodies and Fittings



Make 90° bends while allowing straight pulls! OCAL-BLUE® Double-Coat Pulling Elbows



LBD2200-G

LBD and LBH bodies are installed at 90° bends in rigid conduit to act as pull outlets for conductors that are stiff due to large size or type of insulation and to make 90° bends in conduit system while allowing straight wire pulls in either direction.

- Choose LBD series for ordinary locations and LBH series for hazardous locations
- Coated with a nominal .002" (2 mil) blue urethane on both interior and exterior
- Nominal .040" (40 mil) PVC coating bonded to exterior
- Pressure-sealing sleeves seal connections

Cat. No.	Color
LBD1100 -	—
_ = space for color identifier	
G = Gray	
W = White	
B = Blue	
Custom colors also available.	

ORDINARY LBD SERIES CAT. NO.	HAZARDOUS LBH SERIES** CAT. NO.	PIPE SIZE IN. METRIC SIZE DESIGNATOR*
LBD1100-__	LBH10-__	1/2 16
LBD2200-__	LBH20-__	3/4 21
LBD3300-__	LBH30-__	1 27
LBD4400-__	LBH40-__	1 1/4 35
LBD5500-__	LBH50-__	1 1/2 41
LBD6600-__	LBH60-__	2 53
LBD7700-__	LBH70-__	2 1/2 63
LBD8800-__	LBH80-__	3 78
LBD9900-__	LBH90-__	3 1/2 91
LBD10900-__	LBH100-__	4 103
LBD012-__	—	5 129
LBD014-__	—	6 15

* Metric size designator (ANSI C80.1-1994).

** Ratings prior to PVC coating



BC3-G Mogul



BLB4-G Mogul



BUB3-G Mogul



OCAL-BLUE® Double-Coat Mogul Fittings

Install mogul fittings in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of installation, to provide the longer openings needed when pulling large conductors, to prevent sharp bends and kinks in large conductors or to provide more splicing space.

- Nominal .002" (2 mil) blue urethane on both interior and exterior
- Nominal .040" (40 mil) PVC coating bonded to exterior
- Pressure-sealing sleeves protect connections



BG48-G Replacement Cover

Cat. No.	Color
BC3 -	—
_ = space for color identifier	
G = Gray	
W = White	
B = Blue	
Custom colors also available.	

MOGUL FITTING WITH COVER AND GASKET				REPLACEMENT COVER BG	PIPE SIZE IN. METRIC SIZE DESIGNATOR*
BC CAT. NO.	BLB CAT. NO.	BUB CAT. NO.	BT CAT. NO.	CAT. NO.	
BC3-__	BLB3-__	BUB3-__	BT3-__	BG48-__	1 27
BC4-__	BLB4-__	BUB4-__	BT4-__	BG48-__	1 1/4 35
BC5-__	BLB5-__	BUB5-__	BT5-__	BG68-__	1 1/2 41
BC6-__	BLB6-__	BUB6-__	BT6-__	BG68-__	2 53
BC7-__	BLB7-__	BUB7-__	BT7-__	BG88-__	2 1/2 63
BC8-__	BLB8-__	BUB8-__	BT8-__	BG88-__	3 78
BC9-__	BLB9-__	BUB9-__	BT9-__	BG98-__	3 1/2 91
BC10-__	BLB10-__	BUB10-__	BT10-__	BG98-__	4 103

* Metric size designator (ANSI C80.1-1994).