



Representative

Catalog Number: ST1/2-B
Product ID: 7TAA087990R0447
UPC Number: 70450840584
Status: Active

PVC Coated Liquidtight Conduit Connector, Straight, Pipe Size 1/2 Inch/16 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Light Blue

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - Straight
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	1/2 Inch/16mm
Connection	Straight
Material	Steel
Finish	PVC Coated
Color	Light Blue
Environmental Conditions	Hazardous Locations

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	16mm
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	50
Outer Dimensions (inches)	11.125x6.875x6.5
Weight Uom	0.21 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com