



Actual

Catalog Number: ST3/8-G
Product ID: 7TAA087520R0031
UPC Number: 70450840784
Status: Active

PVC Coated Liquidtight Conduit Connector, Straight, Pipe Size 3/8 Inch/12 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Dark Gray

- A minimum of .040 inch (40 mil) PVC coating is bonded to the exterior.
- Double coated with a nominal .002 inch (2 mil) blue urethane on both the interior and exterior, before PVC coating is applied.
- Pressure-sealing sleeves are designed to protect the connection.
- PVC coated connectors are available in straight, 45 degree and 90 degree configurations
- Ocal uses T&B Industrial Liquidtight fittings to insure quality installations.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - Straight
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	3/8 Inch/12mm
Connection	Straight
Material	Steel
Finish	PVC Coated
Color	Dark Gray
Environmental Conditions	Hazardous Locations

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

Packaging

Outer Quantity	50
Outer Dimensions (inches)	13.8x8x8.45
Weight Uom	15.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com