



Actual

Catalog Number: MINE11/4SA-G
Product ID: 7TAA087000R1084
UPC Number: 70450801153
Status: Active

PVC Coated Mini Conduit Hanger, Pipe Size 1-1/4 Inch/35 Metric, Rated for Loads up to 500 Pounds (226.80 Kilograms) with a Safety Factor of Three, Includes Stainless Steel Bolt and Nut, Aluminum, Dark Gray

North American Specifications (UNSPSC)

UNSPSC	39121701 Electrical hangers
IGCC	5026 Electrical hangers
Brand Name	Ocal
Type	Mini Conduit Hanger
Special Features	Includes Stainless Steel Bolt and Nut for Fast, Easy Installation
Application	Rated for Loads of Up to 500 Pounds/226.80kg with a Safety Factor of Three
Size	1-1/4 Inch/35mm
Material	Steel
Color	Dark Gray
Load	Up to 500 Pounds/226.80 Kilograms

European Specifications (ETIM)

ETIM	EC000464 Fixing clamp
Type of fastening	Clamping
Connection type construction part	Pipe/cable
Tube/cable diameter	35-35mm
Hinging	N
Material	Other
Surface protection	Coated

Packaging

Outer Quantity	50
Outer Dimensions (inches)	11.37x7.12x6.75
Weight Uom	20 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet Canada	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com